



Brand of NTN corporation

## Technical data

### ESPAE203

Bearing units




Grey cast housing, radial insert ball bearing with eccentric locking collar, single lip seal

#### KIT CONTENT

ES203G2, PAE203

#### VISUAL (S)



#### PRODUCT DEFINITION

<b>Brand</b>	SNR
<b>A - Housing width</b>	30 mm
<b>A1 - Housing top width</b>	18 mm
<b>B - Width of Inner Ring</b>	19,1 mm
<b>d - Shaft diameter</b>	17 mm
<b>d1 - Outer dia of eccent. Lock. collar / nut of adapter sleeve</b>	27,2 mm



**NTN Europe**

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
 S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
 SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

**PRODUCT DEFINITION**

<b>E - Mounting hole thread depth</b>	10 mm
<b>G - Grease fitting</b>	M6x1
<b>H - Distance mounting base to centerline spheric. seating diam.</b>	30,2 mm
<b>H1 - Housing foot height</b>	9 mm
<b>H2 - Housing height</b>	57 mm
<b>J - Mounting holes distance</b>	47 mm
<b>L - Housing length</b>	63 mm
<b>L1 - Housing foot length</b>	17,5 mm
<b>N - Mounting hole dimension</b>	M8
<b>S - Distance front side/bearing centre</b>	6,5 mm

**PRODUCT PERFORMANCE**

<b>C - Dynamic load rating</b>	9550000 mN
<b>C0 - Static load rating</b>	4780000 mN
<b>Operating temperature min.</b>	253,15 °K
<b>Operating temperature max.</b>	373,15 °K

**OTHER FEATURES**

<b>Mass</b>	0,43 kg
<b>Recommended tightening torque for set screw</b>	5.5 N-m

