

56019

Ergonomic shovel, 380 x
340 x 90 mm, 1310 mm,
Black



Use this durable Ergonomic Shovel to move large amounts of food waste or food ingredients. Ergonomically designed with the user's working position in mind, this product is ideal for working at floor level as well as shovelling from container to container.

Technical Data

Item Number	56019
Shovel Blade Size, L x W x H	380 x 340 x 90 mm
Material	Polypropylene Anodised Aluminium
Complies with (EC) 1935/2004 on food contact materials ¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates	No
Is Halal compliant	Yes
Box Quantity	1 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	60 Pcs.
Quantity Per Layer (Pallet)	1 Pcs.
Box Length	1310 mm
Box Width	345 mm
Box Height	225 mm
Length/Depth	1310 mm
Width	345 mm
Height	225 mm
Gross Weight	1,86 kg
Net Weight	1,86 kg
Cubik metre	0,1017 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max. usage temperature (for food contact)	100 °C
Max usage temperature (non food contact)	100 °C
Min. usage temperature ³	-20 °C
Max. drying temperature	120 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
GTIN-13 Number	5705020560194
GTIN-14 Number (Box quantity)	5705020560194
Commodity Code	39241000
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care

units, before use.

1. See Declaration of Compliance for further details on food contact

3. Do not store the product below 0° Celsius.