

Features

- *Conductor*
Material: tinsel wires
- *Jacket Material:*
PVC, black
- *Cable Length:*
1.8M
- *Easy to install and reliable connection*
- *Color: Black*

RS PRO Telephone Cable

RS Stock No.: 0707873



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against

demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

This is a coiled RJ11 6P4C to RJ11 6P4C data cable for both data and voice use, coiled length is 230mm, extended length is 1.8M. Extended length coiled cord is provided extra length for working in the office or at home. Both ends are durable RJ11 6P4C connector.

Straight-through pin out for both data and voice use.

It connects Telephones, Fax, Answering Machines to a wall jack or splitter.

General Specifications

<i>Number of Strands</i>	<i>4</i>
<i>Conductor Strand Type</i>	<i>Stranded</i>
<i>Terminated/Unterminated</i>	<i>Terminated; Unterminated</i>
<i>Connector Type</i>	<i>Male RJ11/RJ11</i>
<i>Connector B</i>	<i>Male RJ11</i>
<i>Connector A</i>	<i>Male RJ11</i>
<i>Outer Sheath Material</i>	<i>PVC;</i>
<i>Sheath Colour</i>	<i>Black</i>
<i>Conductor Material</i>	<i>Tinsel Copper wire</i>
<i>Drain Wire</i>	<i>No</i>
<i>Fire Behaviour</i>	<i>Flame Retardant.</i>

Mechanical Specifications

<i>Length</i>	<i>3m</i>
<i>Outer Diameter</i>	<i>5.0*2.5mm</i>
<i>Sheath Thickness</i>	<i>0.6mm</i>

<i>Insulator Diameter</i>	0.9mm +/-0.05
<i>American Wire Gauge</i>	28AWG
<i>Cross Sectional Area</i>	0.079mm ²
<i>Size of Strands</i>	7/0.12mm, 28AWG
<i>Core Strands</i>	7/0.12mm

Approvals

<i>Compliance/Certifications</i>	RoHS, Reach
<i>Declarations</i>	RoHS, Reach

