

Star delta starter, enclosed, 230 V/15 kW, steel

Part no. XSDP15/ST(230V50HZ,240V60HZ)
Catalog No. 118552
Alternate Catalog No. XSDP15-STG3

Delivery program

Product range			enclosed contactor combinations
Application			Star-delta motor starting for contactor combinations
Utilization category			NAC-3: Normal AC induction motors: starting, switch off during running
Max. rating for three-phase motors, 50 - 60 Hz			
AC-3			
380 V 400 V	P	kW	15
Actuating voltage			230 V 50 Hz, 240 V 60 Hz
Voltage AC/DC			AC operation

Technical data ETIM 7.0

Low-voltage industrial components (EG000017) / Combination of contactors (EC000010)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Contactor (LV) / Combination of contactor (ecl@ss10.0.1-27-37-10-09 [AGZ572014])			
Function			Star-delta contactor
Rated control supply voltage Us at AC 50HZ		V	230 - 230
Rated control supply voltage Us at AC 60HZ		V	240 - 240
Rated control supply voltage Us at DC		V	0 - 0
Voltage type for actuating			AC
Rated operation current Ie at AC-3, 400 V		A	29.3
Rated operation power at AC-3, 400 V		kW	15
Rated operation power NEMA		kW	0
Type of electrical connection of main circuit			Screw connection
Degree of protection (IP)			IP55
Degree of protection (NEMA)			Other