


FEATURES

- **Bare Copper Conductor:** Ensures excellent conductivity and signal transmission.
- **Stranded Conductor Type:** Offers enhanced flexibility and resistance to breakage.
- **Polyvinyl Chloride Jacket:** Provides robust protection against environmental factors.
- **6 Core Configuration:** Supports multiple connections within a single cable.
- **Compact Dimensions (2.4 x 6.8 mm):** Facilitates easy installation in tight spaces.
- **REACH and RoHS Compliant:** Meets key safety and environmental standards.

RS PRO 10 m Telephone Cable, 6 Core Stranded

RS Stock No: 707-863



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO telephone cable is designed for reliable and efficient communication applications. With a length of 10 metres, it is ideal for installations requiring extended reach. The cable features a stranded conductor type, providing flexibility and durability, making it suitable for various telecommunication setups.

General Specifications

Conductor Material	Bare Copper
Conductor Type	Stranded
Jacket Colour	Black
Product Type	Telephone Cable

Mechanical Specifications

Cable Length	10 m
Core Strands	7/0.12
Cross Sectional Area	0.079 mm ²
Jacket Material	Polyvinyl Chloride
Number of Cores	6
Outside Diameter	2.4 x 6.8 mm

Approvals

Standards/Approvals	REACH, RoHS
---------------------	-------------