

**Bourdon tube pressure gauges, liquid filling,**

**Modelcode type: 213.53.100**

**Item number: 82467912**

**Description**

Design	EN 837-1
Nominal size	100 mm
Accuracy class	class 1.0
Scale range	0...40 kg/cm <sup>2</sup>
Unit of outer Scale	kg/cm <sup>2</sup>
2nd Scale or Special Scale	2nd scale MPa
Process connection	G 1/4 B
Connector location	lower back mount

**Materials**

Measuring system	copper alloy
Movement	Copper alloy
Dial	Aluminum, white
Pointer	standard pointer
Window	polycarbonate
Bezel ring	roll formed, stainless steel
Case filling fluid	prepared for filling

**Operating conditions**

Permissible ambient temperature	-20 ... +60 °C
Ingress protection	IP 65

**Options**

Mounting flange/bracket	Triangular bezel, stainless steel, polished, with clamp
-------------------------	---

**Labelcode**

Label	WIKA standard without / with Tag-number
language of the label	German