

MFC SERIES - ACTIVATED CARBON FILTER

MFC basic filtration - Activated carbon filtration



Part number	Female thread	Flow rate at 7 bar (m ³ /h) (ΔP= 0,08 bar)	Temperature min/max (°C)	Max. operating pressure (bar)
MFC 55	G1/2	55	5 / 50	20
MFC 70	G1/2	70	5 / 50	20
MFC 100	G1/2	100	5 / 50	20
MFC 150	G3/4	150	5 / 50	20
MFC 225	G 1	225	5 / 50	20
MFC 300	G 1 1/2	300	5 / 50	20
MFC 400	G 1 1/2	400	5 / 50	20
MFC 500	G 2	500	5 / 50	20
MFC 800	G 2	800	5 / 50	20



Part number	Dim. A (mm)	Dim. C (mm)	Dim. D (mm)	Dim. E (mm)
MFC 55	90,00 mm	252,00 mm	230,00 mm	19,00 mm
MFC 70	128,00 mm	273,00 mm	250,00 mm	32,00 mm
MFC 100	128,00 mm	303,00 mm	279,00 mm	32,00 mm
MFC 150	140,00 mm	370,00 mm	335,00 mm	31,00 mm
MFC 225	140,00 mm	398,00 mm	365,00 mm	31,00 mm
MFC 300	140,00 mm	474,00 mm	432,00 mm	31,00 mm
MFC 400	140,00 mm	564,00 mm	522,00 mm	31,00 mm
MFC 500	151,00 mm	511,00 mm	465,00 mm	25,00 mm
MFC 800	151,00 mm	696,00 mm	650,00 mm	25,00 mm