

Features

- Master Keyed
- Anti-drill centre for added protection
- Highly durable brass construction with chrome plating
- Medium physical and manipulation resistance
- Suitable for both indoor or outdoor use
- 500,000 key differs
- Choice of 3 body lengths

RS PRO Camlocks

RS Stock No.: 0597272



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

A master keyed cam lock with an all-brass construction and a chrome plated outer body. With a unique seven-pin locking mechanism, this lock offers good security and key control, and is available with a range of 3 body lengths.

- *Supplied with 2 operator keys per lock*
- *Anti-drill centre for added protection*
- *Medium physical and manipulation resistance*
- *Suitable for both indoor and outdoor use*

General Specifications

Features	Durable brass cam lock
Key Differs	500,000
Mechanism	Unique Radial Pin Tumbler
Body Material	Brass
Finish	Polished Chrome
Key Suite Options	Master Keyed, with keyed alike or keyed to differ
Body Length	18mm, 25mm and 30mm
Fixing Hole Dimensions	Standard 19.1mm x 15mm double D punch
Lock Fixing	2BN brass body nut and a nyloc tail nut
Key Operations	3, 6 and 9 12 o'clock trapped and free key

Mechanical Specifications

Unlock Method	90 degrees clockwise turn, key trapped
Lock Type	Cam lock