

1/4" TORQUE WRENCH PLUS 3 - 15 NM



- 1/4" torque wrench Plus
- $\pm 4\%$ accuracy
- 72-teeth ratchet mechanism (DIN3122) with quick-release button
- Click-type mechanism with clear torque signal
- Ergonomic handle with Nm scale
- Locking button to secure set torque
- Designed for clockwise fastening of right-hand threads
- Twist reverse function for easy direction changes
- Supplied in a practical storage case

The TengTools 1492P015 1/4" torque wrench Plus is specifically designed for professional tasks such as fine-tuning and tightening small fasteners in electronic equipment, precision machinery, or similar applications requiring a tightening torque of 3-15 Nm. The ratchet mechanism has 72 teeth and complies with DIN3122 standard, ensuring reliable and controlled tightening with an accuracy of $\pm 4\%$. The quick-release button allows you to quickly and easily change sockets, making the torque wrench versatile and useful for various types of jobs. The handle of the torque wrench is ergonomic and comfortable with a clear Nm scale that has a resolution of 0.4 Nm, allowing for very precise adjustments of the tightening torque. Additionally, the handle has a locking button that ensures the selected torque does not change accidentally while you work. The torque wrench is designed for clockwise fastening of right-hand threads with a click-type ratchet mechanism that emits an audible signal when the set torque is reached, preventing over-torquing. It also has a twist reverse feature that makes it easy to change direction. The tool weighs only 240 g, is 26 mm wide, and 190 mm long, making it compact and easy to handle. A practical storage case is included to keep it protected during transport and storage. Each torque wrench is assigned a unique number and individually tested to comply with ISO 6789 standards and comes with a 'Declaration of Conformance' for guaranteed accuracy.

General information

Country of origin: Taiwan
Barcode: 5020385033993
Tariff code Europe: 8204120000
ECCN US: EAR99
ETIM: EC002132
UNSPSC: 27111715

Features



Attributes

Product type: Torque Wrenches
Drive: 1/4"
Number of teeth: 72
Range: 3-15 Nm
Scale resolution: 0.4
Accuracy: $\pm 4\%$
Calibration certificate: Factory
Reverse direction: Twist
Preset: No
Angular gauge: No
Digital: No
Bi-directional: No
Mechanism: Click
Tethering facility: No

Dimensions

Net weight (g): 240
Width (mm): 26
Length: 190 mm

DESIGNED IN SWEDEN

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.

Technical changes and errors may occur. 04-02-2025 09:18



Sandbergsvägen 3
 441 39 Alingsås,
 Sweden