

Endress+Hauser Capacitance level switch FTI26-BO4NWDJPA

Capacitive point level switch for powder and fine-grained solids for the food industry.



Picture for reference only. Product appearance may vary based on configuration

The Nivector FTI26 is a point level switch for powdered or granular solids in the food and other industries. The capacitance device offers high sensitivity and build-up performance. Thanks to the compact design, installation is possible even when access is restricted. The optional IO-Link capability allows easy parameter setting.

- Easy installation even in tight conditions or where access is restricted thanks to the compact design
- Fulfillment of all relevant hygienic requirements (3-A, EHEDG, FDA, EG1935/2004)
- No individual adjustment to each medium necessary
- Industry 4.0 ready with IO-Link communication

Configuration of FTI26-BO4NWDJPA:

Approval:	BO	ATEX II 1/3D Ex ta/tc IIIC Da/Dc
Power; Output:	4	12-30VDC; 3-wire PNP
Electrical Connection:	N	Plug M12, IP66/68/69 NEMA Type 4X/6P Encl.
Process Connection:	WDJ	Thread ISO228 G1, 316L
>>Accessory Enclosed:	PA	Protector G1-1/2, PBT-GF

Alternative part number: FTI26-11X0/0