



Part Number : [2136800001](#)
Product Description : Centrality 11.00mm Top-entry, Knurled Press-fit Socket Assembly with +/-1.00mm Self-alignment Capability, Tray
Series Number : 213680
Status : Active
Product Category : PCB Headers and Receptacles



Documents & Resources

Drawings
[2136800001_sd.pdf](#)
[2136800001-PK-000.pdf](#)

3D Models and Design Files
[2136800001_stp.zip](#)

Specifications
[2138800001-PS-000.pdf](#)
[2138800001-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33; 34
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	213680
Description	Sentrality 11.00mm Top-entry, Knurled Press-fit Socket Assembly with +/-1.00mm Self-alignment Capability, Tray
Application	Busbar-to-Board, Busbar-to-Busbar, Power
Comments	Current and voltage performances are dependent upon application variables.
Component Type	PCB Receptacle
Product Name	Sentrality
UPC	195842252875

Electrical

Current - Maximum per Contact	350.0A
Voltage - Maximum	600V

Physical

Breakaway	No
Circuits (Loaded)	1
Circuits (maximum)	1
Diameter	11.00mm
Durability (mating cycles max)	200
Glow-Wire Capable	No
Guide to Mating Part	Yes
Height Above Board	3.40mm

Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Silver
Mating Orientation	Top-entry
Net Weight	15.721/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Tray
PCB Retention	None
Pitch - Mating Interface	N/A
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Press-Fit

Mates With / Use With

Mates with Part(s)

Description	Part Number
Sentrality 11.00mm Screw Mount Pins	<u>213902</u>