



Part Number : [02092170](#)

Product Description : 2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1190, Male, with Tin (Sn) Plated Brass Contact, 18-14 AWG, Large Insulation Crimp, Reel

Series Number : 42138

Status : Active

Product Category : Crimp Terminals

Engineering Number : 42138-(P901)



Documents & Resources

Drawings

[002092170_sd.pdf](#)


[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	42138
Description	2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1190, Male, with Tin (Sn) Plated Brass Contact, 18-14 AWG, Large Insulation Crimp, Reel
Application	Power, Wire-to-Wire
Product Name	Standard .093"
UPC	800753615441

Physical

Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.425/g
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	4.57mm max.
Wire Size (AWG)	14, 16, 18
Wire Size mm ²	N/A

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Use with Part(s)

Description	Part Number
Standard .093" Pin and Socket Dual Row Connector Housings	<u>1261</u>
Standard .093" Pin and Socket 3 Row Connector Housings	<u>1292</u>
Standard .093" Pin and Socket 3 Row Connector Housings	<u>1360</u>
Standard .093" Pin and Socket Single Row Connector Housings	<u>1396</u>
Standard .093" Pin and Socket Single Row Connector Housings	<u>1490</u>
Standard .093" Pin and Socket Single Row Connector Housings	<u>1545</u>
Standard .093" Pin and Socket Single Row Connector Housings	<u>1619</u>

Application Tooling

Global

Description	Part Number
Terminator Die	<u>11402212</u>
Extractor Tool for .093 and HCS-125 Product Series	<u>638240200</u>
Mini-Mac Applicator, Double 18+18 AWG Wires, One Wire Max Insulation 4.32mm and Other Wire Max Insulation 2.79mm	<u>638933000</u>
Mini-Mac Applicator, Insulation O.D. 2.36-4.57mm and 18 AWG SPT-3 Wires	<u>638933100</u>
Mini-Mac Applicator, Double 18+18	<u>638933200</u>

AWG Wires, Insulation Diameter of 2.36-3.56mm Each	
Mini-Mac Applicator, Insulation O.D. 2.36-3.56mm and 18 AWG SPT-3 Wires	<u>638933300</u>

This document was generated on Nov 06, 2025