

WG-D HF 10,2 BK - Cable twist tie



3241102

<https://www.phoenixcontact.com/gb/products/3241102>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable drillers, for fast and tool-free bundling of conductors and cables, removable and reusable



Commercial data

Item number	3241102
Packing unit	500 pc
Minimum order quantity	1,000 pc
Sales key	BE7133
Product key	BE7133
Catalog page	Page 623 (C-3-2019)
GTIN	4046356717311
Weight per piece (including packing)	0.428 g
Weight per piece (excluding packing)	0.409 g
Customs tariff number	39269097
Country of origin	TW

WG-D HF 10,2 BK - Cable twist tie



3241102

<https://www.phoenixcontact.com/gb/products/3241102>

Technical data

Product properties

Product type	Cable tie
Type	Notched strip
Tensile strength GRP	0 N

Dimensions

Width	10.2 mm
Length	26.2 mm

Material specifications

Color	black (RAL 9005)
Material	PA 6.6
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

Cable/line

External cable diameter	7.6 mm ... 10.2 mm
Tensile strength	0 N

Environmental and real-life conditions

Ambient conditions

Optimum ambient temperature (storage/transport)	23.00 °C 50.00 % Polyamide 6.6 has pronounced hygroscopic properties. It absorbs or releases water in accordance with the level of humidity within its environment. Its properties are ideal when the percentage of water is 2 - 3%. The packaging, which is tailored specifically to the product concerned, contains the optimum level of moisture. To ensure that the ideal properties are maintained, the following points should be observed during storage: Keep product stored inside sealed original packaging, carry out any product processing soon after breaking open the packaging, avoid direct sunlight, avoid direct heat.
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (assembly)	-10 °C ... 60 °C
Resistance to UV radiation	no

Mounting

Mounting type	Twist
---------------	-------

WG-D HF 10,2 BK - Cable twist tie



3241102

<https://www.phoenixcontact.com/gb/products/3241102>

Classifications

ECLASS

ECLASS-13.0	27140702
-------------	----------

ETIM

ETIM 9.0	EC000046
----------	----------

UNSPSC

UNSPSC 21.0	39121700
-------------	----------

WG-D HF 10,2 BK - Cable twist tie



3241102

<https://www.phoenixcontact.com/gb/products/3241102>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk