



## MATERIAL FACT SHEET

### 719996 FX5S-60MR/DS

#### General Data

Product Hierarchy	IAD21705
	Compact PLC
	FX5S CPU
Ext. Material Group	10 STANDARD ITEM
ABC Indicator	B (Limited Availability from Stock)

e-shop: <https://emea.mitsubishielectric.com/fa/shop/material-page/000000000000717286>

#### FA-COM PLC: Main Unit

Series	MELSEC IQ-F SERIES
Type	FX5S
Power Supply (V)	24
Current Type	DC
Program Memory	48K STEPS
Program Memory Unit	FLASH
Integrated Digital Inputs	36
Integrated Digital Outputs	24
Output Type	RELAY
Local I/O Points	60
Local + Remote I/O Points	256
Expandable	NO
Cycle Time LD (ns)	84
Cycle Time MOV (ns)	100
USB	1
Ethernet Port	1
Power Consumption (W)	16
Protection Class	IP10
Min. Ambient Temperature (°C)	-20
Max. Ambient Temperature (°C)	55

#### Logistic Dimensions & Gross Weight

Length (cm)	23,0
Width (cm)	15,0
Height (cm)	11,0
Gross Weight (kg)	0,700
Volume (cdm)	5,100

#### Stock Data

Planned Delivery Time (Days)	77
------------------------------	----

#### Life Cycle

Sales Start	28.06.2024
Predecessor	<a href="#">231477 / FX3G-60MR/DS</a>

#### Additional Product Information

Battery included	NO
------------------	----

#### Export Data

Commodity Code	85371091
Legal Control (Dual Use List)	Not Listed
Country of Origin	Japan (JP)
Preference Status (Supplier Declaration)	Non EU

#### Environmental

REACH Limit Exceeded	YES
----------------------	-----

REACH Substance CAS Number	<a href="#">12060-00-3</a>
REACH Substance CAS Number (2)	<a href="#">629-14-1</a>
REACH Substance CAS Number (3)	<a href="#">7439-92-1</a>
Dangerous Goods Class	NO
Dangerous Goods Identifier	NO
RoHS Compliance	COMPLIANT
WEEE	B2B

### Conformity

CE	COMPLIANT
EAC	NON-COMPLIANT

### Documentation & Media Data

Manual URL Indicator	<a href="https://emea.mitsubishielectric.com/fa/advanced-search?ct=document&amp;doc-cats=bltdae25c2bd5f2ff94&amp;q=FX5S-60MR/DS&amp;doc-lang=en">https://emea.mitsubishielectric.com/fa/advanced-search?ct=document&amp;doc-cats=bltdae25c2bd5f2ff94&amp;q=FX5S-60MR/DS&amp;doc-lang=en</a>
Certificates URL Indicator	<a href="https://emea.mitsubishielectric.com/fa/advanced-search?ct=document&amp;doc-cats=blt8050dd1408c11cc2&amp;q=FX5S-60MR/DS&amp;doc-lang=en">https://emea.mitsubishielectric.com/fa/advanced-search?ct=document&amp;doc-cats=blt8050dd1408c11cc2&amp;q=FX5S-60MR/DS&amp;doc-lang=en</a>
CAD URL Indicator	<a href="https://emea.mitsubishielectric.com/fa/advanced-search?ct=document&amp;doc-cats=blt26ecc97a31a841c1&amp;q=FX5S-60MR/DS&amp;doc-lang=en">https://emea.mitsubishielectric.com/fa/advanced-search?ct=document&amp;doc-cats=blt26ecc97a31a841c1&amp;q=FX5S-60MR/DS&amp;doc-lang=en</a>

### Product Packaging

Cardboard (g)	147
Other paper (g)	3,35
Aluminum (g)	0
Steel (g)	0
Styrofoam (g)	0
Other plastic (g)	0
Wood (g)	0
Glass (g)	0
Others (g)	0

### Compatible products

Material	Description / Price List Text / Classification
<a href="#">697551</a>	IE-C6A-0.2m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 0.2m, for Cabinet Class 100100214: FA-MOD PLC: Cable
<a href="#">697582</a>	IE-C6A-0.5m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 0.5m, for Cabinet Class 100100214: FA-MOD PLC: Cable
<a href="#">697583</a>	IE-C6A-1.0m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 1.0m, for Cabinet Class 100100214: FA-MOD PLC: Cable
<a href="#">697584</a>	IE-C6A-2.0m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 2.0m, for Cabinet Class 100100214: FA-MOD PLC: Cable
<a href="#">697585</a>	IE-C6A-5.0m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 5.0m, for Cabinet Class 100100214: FA-MOD PLC: Cable
<a href="#">697586</a>	IE-C6A-10.0m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 10.0m, for Cabinet Class 100100214: FA-MOD PLC: Cable
<a href="#">697587</a>	IE-C6A-15.0m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 15.0m, for Cabinet Class 100100214: FA-MOD PLC: Cable
<a href="#">697588</a>	IE-C6A-20.0m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 20.0m, for Cabinet Class 100100214: FA-MOD PLC: Cable
<a href="#">697589</a>	IE-C6A-25.0m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 25.0m, for Cabinet Class 100100214: FA-MOD PLC: Cable
<a href="#">697590</a>	IE-CB-1piece CC-Link Bending tool for Patch Cable, RJ45, 1 piece, 90°Deg radius Class 100100215: FA-MOD PLC: Other Option
<a href="#">697591</a>	IE-C6A-CON-1pc CC-Link IE Certified Patch Cable connector, easy clip, RJ45, Cat.6A, 1pc Class 100100215: FA-MOD PLC: Other Option
<a href="#">717285</a>	EDS-G2008-EL 8Port Entry-level Unmanaged Switch, 10/100/1000BaseT(X), CCLink IE Field/TSN Cl. A Class 100100211: FA-MOD PLC: Network Module

Material	Description / Price List Text / Classification
<a href="#">717286</a>	EDS-G2005-EL 5Port Entry-level Unmanaged Switch,10/100/1000BaseT(X),CCLink IE Field/TSN Cl. A Class 100100211: FA-MOD PLC: Network Module