

Hynit®

32-125

Good resistance to abrasion with remarkable flexibility



Oil



Light Duty

Light, comfortable and abrasion-resistant gloves providing food handling compliance

- **Improved durability and flexibility:** Hynit® 32-125 industrial gloves utilize a special nitrile formulation that afford superior abrasion resistance and flexibility
- **Added protection:** Thanks to their liquid-repellent impregnation, these safety gloves resist oil, grease and dirt, enhancing personal protection
- **Food handling compliance:** In addition, Hynit® 32-125 hand protection gloves are compliant with FDA food handling requirements



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Mining

Applications

- Assembly & inspection of components
- Delivery of parts to production line
- Seizing structural parts
- Loading and unloading rough parts or boxes
- Final assembly
- Handling application & cleaning tools
- Shipping and loading of product



32-125

Good resistance to abrasion with remarkable flexibility

Key Features

- **Special nitrile formulation:** Improves durability and flexibility
- **Liquid-repellent impregnation:** Resists oil, grease and dirt
- **FDA-approved:** Complies with FDA food handling requirements

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



3111A

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
Hynit® 32-125	Finishing: Fully Impregnated Coating Material: Nitrile Liner Material: Cotton, Polyester Cuff Style: Slip-on - Perforated Back	N/A	6.5, 7, 7.5, 8, 9, 10	208-237 mm/8.2-9.3 inches	Blue	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

