

MG-INC-M20-S67L-PTES-LG - Membrane screw connection



1415187
<https://www.phoenixcontact.com/gb/products/1415187>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Membrane screw connection, material for screw connection: Polypropylene, application: Standard, external cable diameter 6 mm ... 13 mm, shielding: no, connecting thread: M20, color: light gray

Commercial data

Item number	1415187
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	AF7DFX
Product key	AF7DFX
Catalog page	Page 693 (C-2-2019)
GTIN	4055626038018
Weight per piece (including packing)	4.68 g
Weight per piece (excluding packing)	3.554 g
Customs tariff number	39269097
Country of origin	DE

MG-INC-M20-S67L-PTES-LG - Membrane screw connection



1415187

<https://www.phoenixcontact.com/gb/products/1415187>

Technical data


Mounting

Assembly note	for 0.8 mm ... 3.5 mm wall thickness, for 20 mm ... 20.7 mm bore hole
---------------	---

Product properties

Product type	Cable screw gland
Application	Standard
Manufacturer	WISKA
Manufacturer Designation	CLIXX 20
Shielded	no

Dimensions

Dimensional drawing	
Length	15 mm
Length of the connecting thread	8 mm
Length without connecting thread	7 mm
Diameter	20 mm
Connecting thread diameter	20 mm
Hole diameter	20 mm ... 20.7 mm
Hexagon angular dimension	34 mm
Thread type connection side	M20

Material specifications

Color	light gray (RAL 7035)
Seal material	TPE
Material for screw connection	Polypropylene

Cable/line

External cable diameter	6 mm ... 13 mm
-------------------------	----------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
	IP67
Ambient temperature (operation)	-40 °C ... 65 °C


MG-INC-M20-S67L-PTES-LG - Membrane screw connection



1415187

<https://www.phoenixcontact.com/gb/products/1415187>

Drawings



MG-INC-M20-S67L-PTES-LG - Membrane screw connection



1415187
<https://www.phoenixcontact.com/gb/products/1415187>

Classifications

ECLASS

ECLASS-13.0	27140890
-------------	----------

ETIM

ETIM 9.0	EC000441
----------	----------

UNSPSC

UNSPSC 21.0	39121300
-------------	----------

MG-INC-M20-S67L-PTES-LG - Membrane screw connection



1415187

<https://www.phoenixcontact.com/gb/products/1415187>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk