



Part Number : [192770003](#)
Product Description : Quixon Quick Disconnect,
Avikrimp Style, Female, Fully Insulated Red, 22-18
AWG, Mylar Tap
Series Number : 19277
Status : Active
Product Category : Quick Disconnects
Engineering Number : AA-5261T-LIF



Documents & Resources

Drawings

[192770003 sd.pdf](#)


Specifications

[PS-19902-012-001.pdf](#)

[PS-19902-015-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19277
Description	Quixon Quick Disconnect, Avikrimp Style, Female, Fully Insulated Red, 22-18 AWG, Mylar Tap
Comments	Low Insertion Force
Product Name	Avikrimp,Quixon
Type	Quick Disconnect
UPC	884982565180

Agency

CSA	LR18689
UL	E79133

Electrical

Voltage - Maximum	300V
-------------------	------

Physical

Barrel Type	Closed
Color - Resin	Red
Flammability	94V-2
Gender	Female
Glow-Wire Capable	No
Insulated	Fully
Insulation	Nylon (PA)

Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.039/g
Orientation	Straight
Packaging Type	Embossed Tape on Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Tab Thickness	0.41mm
Tab Width	7.87mm
Temperature Range - Operating	-55° to +105°C
Wire Insulation Diameter	3.00mm
Wire Size (AWG)	18, 20, 22

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>192880028</u>
Mini-Mac Applicator	<u>638852000</u>