

1610-B
Pre-insulated ring terminals

	art.	D mm	 mm ²	L mm
BM00119	BM00119	4	0,25-1,5	20,6
BM00125	BM00125	5	0,25-1,5	21,8
BM00225	BM00225	5	1,5-2,5	22,4
BM00231	BM00231	6	1,5-2,5	26
BM00237	BM00237	8	1,5-2,5	29,8
BM00331	BM00331	6	4-6	29,1
BM00337	BM00337	8	4-6	34,5

