

C-SCFFI 1,5/2,8X0,5 - Connector



3240534

<https://www.phoenixcontact.com/gb/products/3240534>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Slip-on sleeve, fully isolated, red, 0.5 ... 1.5 mm², for plug 2.8 x 0.5 mm

Your advantages

- Hard-soldered crimping zone for maximum conductor pull-out forces in connection with CRIMPFOX RCI... pliers
- Easy and reliable conductor entry thanks to 'EASY ENTRY'
- Halogen-free
- Electrogalvanized

Commercial data

Item number	3240534
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BH3451
Product key	BH3451
Catalog page	Page 500 (C-3-2019)
GTIN	4046356528047
Weight per piece (including packing)	0.81 g
Weight per piece (excluding packing)	0.416 g
Customs tariff number	85366990
Country of origin	CN

C-SCFFI 1,5/2,8X0,5 - Connector

3240534

<https://www.phoenixcontact.com/gb/products/3240534>




Technical data

Product properties

Product type	Connector
Product property	Halogen-free
	With "Easy Entry" (conical insertion area)
	Brazed
	PA-insulated
	Tin-plated
	Temperature range: -20°C ... +105°C
	Flammability rating V2 in accordance with UL 94

Dimensions

Dimensional drawing	
Width	2.8 mm
Sleeve length	19 mm
Length of the insulating material sleeve	10.5 mm
Maximum stripping length	7 mm
Min. material thickness	0.25 mm
Inner dimensions of the insulating collar	4.3 mm

Material specifications

Color	red (RAL 3001)
Material	Brass
Flammability rating according to UL 94	V2
Coating	electrogalvanized
Insulating material	PA
Components	halogen-free

Mechanical properties

Technical data

Sleeve length	19 mm
---------------	-------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 105 °C
Permanent temperature	105 °C
Short-term temperature	120 °C

C-SCFFI 1,5/2,8X0,5 - Connector

3240534

<https://www.phoenixcontact.com/gb/products/3240534>



Drawings

Dimensional drawing



C-SCFFI 1,5/2,8X0,5 - Connector



3240534

<https://www.phoenixcontact.com/gb/products/3240534>

Classifications

ECLASS

ECLASS-13.0	27400204
-------------	----------

ETIM

ETIM 9.0	EC001052
----------	----------

UNSPSC

UNSPSC 21.0	27121700
-------------	----------

C-SCFFI 1,5/2,8X0,5 - Connector

3240534

<https://www.phoenixcontact.com/gb/products/3240534>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk