

## FEATURES

- **S2 Alloy Steel Construction:** Provides exceptional strength and durability, extending the lifespan of the bit
- **4 mm Drive Size:** Ensures compatibility with a wide range of tools and applications
- **Phillips PH2 Size:** Offers a secure fit for standard Phillips screws, reducing the risk of cam-out
- **40 mm Overall Length:** Allows for easy access in tight spaces
- **10-Piece Set:** Provides versatility and convenience for various tasks

## RS PRO 4 mm Phillips Screwdriver Bit, S2 Alloy Steel

RS Stock No: 630-908



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

The RS PRO 4 mm Phillips Screwdriver Bit is designed for precision and durability in various fastening applications. Made from high-quality S2 alloy steel, this screwdriver bit ensures long-lasting performance and reliability. Ideal for both professional and DIY use, it provides a secure fit and efficient torque transfer.

## General Specifications

|                  |                 |
|------------------|-----------------|
| Drive Size       | 4 mm            |
| Drive Type       | Phillips        |
| Number of Pieces | 10              |
| Product Type     | Screwdriver Bit |
| Size             | PH2             |

## Mechanical Specifications

|                |                |
|----------------|----------------|
| Material       | S2 Alloy Steel |
| Overall Length | 40 mm          |

## Approvals

|                     |                                   |
|---------------------|-----------------------------------|
| Standards/Approvals | ANSI-ESD S20.20:2021, REACH, RoHS |
|---------------------|-----------------------------------|

