

FEATURES

- 3 speed fan to accommodate a range of airflow requirements
- Energy saving motor with low noise
- Metal blade with radial guard
- Durable U shape base for improved stability on the floor
- Stylish chrome design
- Portable and user friendly

RS PRO Floor Fan 450mm blade diameter 3 speed 230 V ac with plug: BS

RS Stock No.: 179-2262



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This high velocity floor fan from our reliable and trusted own brand RS PRO provides a powerful cool air flow and is ideal for use in a range of environments such as at home or in an office that requires an excellent source of air cooling and air circulation.

General Specifications

Fan Type	Floor
Air Flow	70/80/100 m3/min
Blade Span	450mm
Number of Speeds	3
Material	Steel
Finish	Chrome
Adjustable Stand	No
Special Features	Energy Saving Motor, Quiet Performance, 3-in-1 Fan Creates a Powerful Wide Cooling Breeze
Non-Slip Base	Yes
Applications	In an office, At home, In a school, Stage performance, Sheltered outdoor use (balcony, patio)

Electrical Specifications

Power Source	Mains powered
Supply Voltage	230VAC
Plug Type	BS
Power Consumption	120W
Speed	Rotary switch 3 speed Speed 1: 7.77m/s , Speed 2: 8.43 m/s, Speed 3: 9.01m/s

Approvals

Compliance/Certifications	CE / GS Approved
----------------------------------	------------------

RS Article	Global Description
1792262	18" High Velocity Floor Fan , BS Plug
1792263	18" High Velocity Floor Fan ,VDE Plug

