



ENGLISH

Datasheet

Trailing Socket 6 NF +USB 1.5m switched



31/07/2017

**RS Stock Number:****Specifications:**

<b>Electrical Rating</b>	<b>16A 250V</b>
<b>Dielectric Strength</b>	<b>1000VAC for 1 min between current carrying parts</b> <b>2500VAC for 1 min between non-current carrying parts</b>
<b>Operating Temperature</b>	<b>-20 ~ +80°C (-4 ~ 176°F)</b>
<b>Degree of Protection</b>	<b>IP20/NEMA 1</b>

**Features:**

- **NF/CE Certified**
- **Trailing Socket 6 NF +USB 1.5m switched**
- **1.5meter, H05VV-F, 3G1.5MM cable**