

Main

Range of product	Mureva Styl
Product or component type	Fixing frame
Range compatibility	Mureva Styl
Colour tint	Grey (RAL 7016)

Complementary

Device mounting	Flush
Number of gangs	1 gang
Condition of use	Indoor/outdoor
Material	PC
Length	84 mm
Height	44 mm
Width	84 mm
Projecting depth	19 mm
Chemical and detergent products resistance	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Quality labels	AENOR NF
IP degree of protection	IP55
IK degree of protection	IK08
Flame retardance	Self-extinguishing 650 °C conforming to IEC 60695-2-1
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-25...55 °C

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration