

## 306 85

### Ring slogging spanner

|                       |             |
|-----------------------|-------------|
| Code                  | ETIM        |
| 6476590               | EC002188    |
| EAN                   | UNSPSC      |
| 4010886647653         | 27-11-17-05 |
| Country of origin     | eCl@ss      |
| Germany               | 21-04-01-03 |
| Customs tariff number |             |
| 82041100              |             |



### Article description

- Top-grade industrial quality for the hardest of continuous use
- For heavy-duty work
- Special sizes available on request up to 250 mm
- Up to length 435 mm made of chrome vanadium steel 31CrV3, from length 480 mm made of material C35
- \* not standardised
- Acc. to DIN 7444

### Article information

|                          |          |                           |          |
|--------------------------|----------|---------------------------|----------|
| Contents (Qty of pieces) | 1        | Standard                  | DIN 7444 |
| Net weight [kg]          | 3,895 kg | Width across flats 1 [mm] | 85       |
| Total length [mm]        | 360 mm   | Head height 1 [mm]        | 37 mm    |
| Surface                  | oiled    | Width of head 1 [mm]      | 129,0 mm |
| Material                 | 31CrV3   | Ring profile              | bi-hex   |