



D4GS-N1R-5

Safety door switch, D4GS-N, IP67, 1NC/1NO (slow-action), horizontal key insertion, 5 m cable

Specifications

Door switch type	Key-operated
Guard-lock	×
Ambient temperature (operating)	-30-70 °C
Direction of operation	Horizontal
Door contacts NC	1
Door contacts NO	1
LED indicator	×
Connection method	Cable
Cable length	5 m
Degree of protection (IP)	IP67
Conduit size	Not Applicable
Number of conduits	0
Switch action	Slow action
Shape	Cuboid
Overall length of sensor	85 mm
Height of sensor	17 mm
Width of sensor	30 mm

Accessories



D4GS-NK1

Operation Key for D4GS-N, horizontal mounting



D4GS-NK4

Operation Key for D4GS-N, adjustable mounting, vertical upward

Downloads

CAD Library



**D4GS-N
Instruction Sheet**

EN PDF 1.55 MB



**D4GS-N Slim Safety
Door Switch
Datasheet**

EN PDF 2.51 MB



**EAC Mark removal
Discontinuation Notice**

EN PDF 221 KB



**Machine Safety
Catalogue**

EN PDF 9.91 MB



**Safety Component
Selection Guide EU
Brochure**

EN PDF 5.26 MB



**Safety Interlock
Switches
Brochure**

EN PDF 1.52 MB



**Safety Solution
Advanced Guide
Guide**

EN PDF 2.57 MB



**Safety Solution Basic
Guide
Guide**

EN PDF 14.4 MB

TERMS OF WEBSITE USE

This PDF document was created from the European OMRON Industrial Automation website on 10 January, 2026. Click here for [terms of use](#).

OMRON

INDUSTRIAL AUTOMATION | [INDUSTRIAL.OMRON.EU](https://www.industrial.omron.eu)