



Part Number : [732870315](#)  
Product Description : 2.92mm Attenuator,  
Plug to Jack, Straight, 40 GHz, 0.5 Watt, 10 dB,  
with Hex  
Series Number : 73287  
Status : Active  
Product Category : RF / Coaxial Connectors



## Documents & Resources

Drawings  
[732870315\\_sd.pdf](#)

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

## Part Details

### General

Status	Active
--------	--------

Category	RF / Coaxial Connectors
Series	73287
Description	2.92mm Attenuator, Plug to Jack, Straight, 40 GHz, 0.5 Watt, 10 dB, with Hex
Keyword	Attenuators
Product Name	2.92mm
Style	Attenuator
Type	Subminiature
UPC	198282631637

## Electrical

Attenuation Level (dB)	10
Average Power Max (Watts)	0.5
Frequency	40 GHz
Impedance	50Ω
VSWR (max)	1.40:1

## Physical

Body Style	With Hex
Gender	Plug/Jack
Keying to Mating Part	N/A
Orientation	Straight
Packaging Type	Bag
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	N/A
Wire/Cable Type	N/A