



Main

Range	Odace
Product or component type	Trailing lead
Aesthetic name	Odace extend
Control type	Mains switch
Integrated connection type	2 USB type A 5 V DC, maximum load current: 2.4 A
Colour tint	White/aluminium bronze
Cable length	1.5 m

Complementary

Type of USB power supply	USB type A + A
[Ue] rated operational voltage	250 V
[In] rated current	16 A
Outlet poles configuration	2P + E
Outlet standard deviation	French
Socket additional information	Shuttered
Maximum switching capacity	16 A
Pilot light	ON indicator
Material	PC PP (polypropylene)
Length	339 mm
Width	57 mm
Depth	40.5 mm
Type of packing	Blister
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane
Height	339 mm
Socket number	5
Surface treatment	Untreated
Number of USB connection	2

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information