

COBArib

Best-selling ribbed runner for floors and workbenches

- Widely used for many different industrial applications, as floor matting or workbench/tool protection.
- Ribbed rubber surface provides additional grip reducing the risk of slipping for operatives.
- Provides a protective covering for workbenches, cushioning the impact of tools and apparatus.
- Also useful for protecting stock at packing stations, and components in assembly areas.
- Can be helpful in supporting noise insulation initiatives.





Parts

Part Number	Size	Colour	Weight (kg)
RR010010	0.9 m x 10 m (3 mm)	Black	26
RR010010C	0.9 m x per linear metre (3 mm)	Black	2.6
RR010020	1.2 m x 10 m (3 mm)	Black	34
RR010020C	1.2 m x per linear metre (3 mm)	Black	3.4
RR010030	0.9 m x 10 m (6 mm)	Black	63.8
RR010030C	0.9 m x per linear metre (6 mm)	Black	6.38
RR010040	1.2 m x 10 m (6 mm)	Black	85.2
RR010040C	1.2 m x per linear metre (6 mm)	Black	8.52

Technical Specifications

Material	Natural rubber
Surface Finish	Fine fluted ribs
Product Height	3 mm, 6 mm
Roll Length	10 m
Min. Operating Temperature	-20°C
Max. Operating Temperature	+80°C
Resistance to Chemicals	Resistant to water and most mild acids
Environmental Resistance	Suitable for wet and dry environments, indoors or outdoors
UV Resistance	Yes

Typical Applications	Workbenches, Workstations, Walkways
Installation Method	Loose lay
Cleaning Method	Hose down or pressure wash using a mild detergent
COO (Country of Origin)	CN