

Datasheet

RS Pro Micro Plug M11 2 pole Screw terminal IP68 10A 400V 1 cable entry

RS Stock No: 136-9901



SPECIFICATION

Type	Plug
Cable Entries	1
Number of Poles	2
Terminal Type	Silver-plated brass (zinc-plated screws)
Body Material	PA66 GF UL94 V0
IP Rating	68
Max Current (A)	10
Max Voltage (V)	400
Minimum Temp Rating °C	-40
Max Temp Rating °C	125
Fixing System	Cable
Temperature "T" Rating	T125