



Passive Components > Resistors > Surface Mount Resistors > SMD Power Resistor: 3 Watt, 5% Tol



Resistance Value: 22K Ω

Resistor Type: Power Resistor

Element Type: Thick Film

Package Size Code: 2512

Power Rating: 3 W

[All SMD Power Resistor: 3 Watt, 5% Tol \(67\)](#)

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Thick Film
Package Size Code	2512

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Resistance Value	22K Ω
Power Rating	3 W
Resistance Class	1k Ω – 1M Ω
Passive Component Tolerance	5 %

Termination Features

Surface Mount Resistor Termination Type	Solder
---	--------



Number of Terminations2

Dimensions

Product Height	1.1 mm[.043 in]
Product Length	6.35 mm[.25 in]
Product Width	3.2 mm[.126 in]

Usage Conditions

Temperature Coefficient	±100 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts





TE Part # 4-2176230-2

3522 2K2 5% 3W



TE Part # CAT-C339-A76B

SMD Power Resistor: 3 Watt, 1% Tol

Also in the Series | CGS 3522



Surface Mount Resistors(211)

Customers Also Bought




TE Part #172142-3

EIS LOW PROFILE HSG 3P NATURAL



TE Part #170369-1

LOW PROFILE EI CONN LP



TE Part #796683-5

TERMI-BLOK PCB MOUNT 90 5P.




TE Part #5-1624113-6

3650 0805 0.30uH 5% 2K RL



TE Part #1437720-6

T01-0580-S07-FEMALE REC PANEL MNT SOLDER



TE Part #2-2176236-6

CPF A 0402 10K 0.1% 25PPM 5K RL



TE Part #4-2176230-2

3522 2K2 5% 3W




TE Part #4-2176231-5

3522 680R 1% 3W



TE Part #1-1879233-8

SMW5 R51 5%



TE Part #281699-4

HEADER HE13 RA 4 P



Documents

Product Drawings

3522 22K 5% 3W

English

CAD Files

Customer View Model

ENG_CVM_CVM_5-2176230-4_BA.3d_stp.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-2176230-4_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5-2176230-4_BA.3d_igs.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SMD POWER RESISTORS - TYPE 3522 SERIES

English