



PRODUCT NUMBER: NK803

Nitri Knit - NK803

Mechanical and chemical resistance to a large range of products (oils, detergents and many solvents). Preparation of greasy products, production of paints, varnishes.

Honeywell

Overview

Reference Number

NK803

Product Type

Gloves

Range

Chemical Protection

Line

Heavy chemical

Brand

Honeywell

Brand formerly known as

NORTH

Industry

- Agriculture
- Automotive and Part Manufacturer
- Chemical Industries
- Industrial Cleaning
- Laboratory
- Offshore
- Petro-chemical
- Water treatment

Product Use

Mechanical and chemical resistance to a large range of products (oils, detergents and many solvents). Preparation of greasy products, production of paints, varnishes.

Features & Benefits

Feature

Supported nitrile glove. Cotton interlock liner. Textured finish. Length : 30 cm.

Benefit

COMFORT Interlock knit liner gives gloves added strength for resistance to cuts, snags, abrasions and punctures while adding comfort to wearer. Hand portion is treated with a permanent anti-bacterial and anti-mildew agent. Unique textured finish provides excellent grip on oily, wet or dry objects. **RESISTANCE** High nitrile content offers superior resistance to cuts, snags, abrasions and punctures. Outperforms supported natural rubber, neoprene and vinyl gloves when exposed to solvents, caustics and animal fats True dip coated glove has a permanent bond of nitrile to inner-liner. Won't peel apart like glued-in liners. **HYGIENE** Gloves are free of latex proteins which can cause allergic reactions.

Technical Description

Description

Supported nitrile glove. Cotton interlock liner. Textured finish. Length : 30 cm.

Product Technology

Dipped

Glove/liner color

Blue

Coating Type

Nitrile

Length

30 cm

Thickness

1 mm

Harmlessness

In conformity with the European standards.

Dexterity

Class 5

Sizes

7S, 8M, 9L, 10XL

EN 388 - Mechanical Hazards Abrasion Resistance

Abrasion resistance	3
Cutting resistance (Coupe test)	1
Tear resistance	1
Puncture resistance	1
Cutting resistance (TDM test)	X

EN ISO 374-1 Resistance to

Resistance to permeation by chemicals	Type B - JKOPT
---------------------------------------	----------------

Certifications

EU Category PPE

3

EU Certification

18/0628/00/0161

Additional Information

User Manual

UI 104

Maintenance

Care Instructions

This article can be cleaned. For cleaning instructions, please contact Honeywell safety products.

© Honeywell International Inc.