

**BOSCH**

Invented for life

# Product data sheet

## Power tools for trade & industry

Cordless Rotary Hammer with SDS max

# PRO GBH 18V-40 C



Cordless freedom with corded performance - SDS max all-rounder for concrete chiselling and drilling up to 40mm

### The most important data

Battery voltage	18.0 V
Impact energy	9 J
Drilling dia. in concrete with hammer drill bits	12 – 40 mm

**Part Number** 0 611 917 100

## Technical data

### Technical data

Impact energy	9 J
Impact rate at rated speed	0 – 3,130 bpm
Rated speed	0 – 360 rpm
Battery voltage	18.0 V
Weight excl. battery	7 kg
Tool holder	SDS max
Packaging dimensions (width x length x height)	395 x 607 x 179 mm
Impact energy nominal	9 J

### Drilling range

Drilling dia. in concrete with hammer drill bits	12 – 40 mm
Opt. app. range in concrete with hammer drill bits	18 – 32 mm

### Drilling range

Drilling dia. in concrete with hammer drill bits	12 – 40 mm
Opt. app. range in concrete with hammer drill bits	18 – 32 mm

## Noise/vibration information

### Hammer drilling in concrete

Vibration emission value ah	9.2 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>

### Chiselling in concrete

Vibration emission value ah	7.6 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>



**BOSCH**

Invented for life

# Product data sheet

Power tools for trade & industry

## Advantages:

- BITURBO Brushless technology with ProCORE18V for corded performance providing powerful 9.0 J impact energy
- Optimal power-to-weight ratio due to an improved impact mechanism and highly capable drive train
- Minimised hand and arm injuries by instantly shutting down the rotary hammer thanks to KickBack Control



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

