





ECN MARK	ECN NO.	DESCRIPTION	DATE



**5P+4C(30AWG)
1.4 Version**

LENGTH
7500mm
5000mm
3000mm
2000mm
1000mm

Type A Pin	Signal Assignment	Type A Pin
1 Blue	Blue 1	Blue 1
2 ground	ground 2	ground 2
3 white	white 3	white 3
4 Blue	Blue 4	Blue 4
5 ground	ground 5	ground 5
6 white	white 6	white 6
7 Blue	Blue 7	Blue 7
8 ground	ground 8	ground 8
9 white	white 9	white 9
10 Blue	Blue 10	Blue 10
11 ground	ground 11	ground 11
12 white	white 12	white 12
13 Blue	Blue 13	Blue 13
14 ground	ground 14	ground 14
15 white	white 15	white 15
16 Yellow	Yellow 16	Yellow 16
17 Orange	Orange 17	Orange 17
18 white	white 18	white 18
19 red	red 19	red 19
SHELL	SHELL	SHELL

FEATURES

1. Gold-plated plugs
2. compliant ROHS. 1080P

ELECTRICAL SPECIFICATION:

1. Withstanding voltage: 300VDC 0.1SEC
2. Insulation Resistance: 3Mohm 300VDC

ITEM	DWG NO	DESCRIPTIONS&SPECIFICATIONS	QTY.	REMARK	TOLERANCE	SIGNATURES	DATE	CPHD006								
5		HDMI Cable 5P+4C OD: 3.5*13.0	1PC		20-00 ±00.00			<table border="1"> <thead> <tr> <th>SCALE</th> <th>TITLE</th> <th>REV</th> </tr> </thead> <tbody> <tr> <td>A1</td> <td></td> <td></td> </tr> </tbody> </table>			SCALE	TITLE	REV	A1		
SCALE	TITLE	REV														
A1																
4		PVC BLACK 4SP	1PC		100-000 ±30.0	DRAFT: Jay										
3		PVC BLACK 4SP	1PC		1000-0000 ±00.00	CHECKED: Neo										
2		HDMI TYPE A PLUG 19PIN (Pins Gold-Plated, SHELL Gold-Plated)	1PC		10000-0000 ±1000.00	APPROVAL:										
1		HDMI TYPE A PLUG 19PIN (Pins Gold-Plated, SHELL Gold-Plated)	1PC													
					Unit:MM		REV	A1	DWG NO	3006-BX001						