

Datasheet

## RS Pro 750mA Axial T Non-Resettable Wire Ended Fuse, 250 V ac

RS Stock No: **764-9545**



### Product Details

RS Pro axial non-resettable fuse withstands currents up to 750 mA. This wire-ended fuse offers T speed with a voltage rating of 250 V ac. It has epoxy-coated body for added durability. The slow blow fuse forms a convenient and reliable solution to a vast array of application requirements.

### Features and Benefits

- FF speed fuse
- Non-resettable
- Axial
- Wire-ended

**Specifications:**

Body Diameter	3.18 mm
Body Height	7.1 mm
Body Material	Epoxy Coated
Breaking Capacity (at Maximum Voltage Rating)	50 A at 250 V ac/125 V dc
Current Rating	750 mA
Fuse Speed	T
Lead Orientation	Axial
Maximum Operating Temperature	+125°C
Minimum Operating Temperature	-55°C
Voltage Rating	250 V ac
Voltage Rating	250 V ac
Wire Diameter	0.64 mm
Wire Length	28 mm
Fuse Type	Slow Blow
Nominal Resistance	0.1733 Ω
Standards Met	RoHS Compliant