



PRODUCT-DETAILS

UPS PowerValue 11LI Up 800 VA

UPS PowerValue 11LI Up 800 VA



General Information	
Extended Product Type	UPS PowerValue 11LI Up 800 VA
Product ID	4NWP100171R0001
EAN	7640169262616
Catalog Description	UPS PowerValue 11LI Up 800 VA
Long Description	VI UPS PowerValue 11LI Up 800VA/480W:230V:50/60Hz:simulated sinewave:1.5 min

Material Compliance	
Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	4NWD004620
RoHS Information	4NWD004317
RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
SCIP	a670f830-777f-4b36-b3b0-267df370e80a Switzerland
Simplified SCIP	287e26df-c773-4cd1-abac-d5541f6e0148 Germany cc87875c-838e-4faa-b144-5fae77325bb1 France e05dd807-5001-4b25-82d6-78c0b3c6442a Netherlands 466b05c1-678f-407a-9295-3cd8430b9d5f Spain 047359aa-beeb-4a20-91cf-85a491b0be35 Netherlands cad3f8af-3f58-4603-a27f-54eea6e1929b Germany

0974efaa-b231-4051-959f-c9372753c053	Denmark
d0922cc9-831f-4d0a-917f-e6f8f59c7687	Poland
23d84147-e808-42fc-a46c-1a178eca51ed	Norway
21c7005d-4646-4e54-bd8e-ac0c43883bad	Finland
9d15a7f5-9796-4d2d-ad56-e1310e7f1613	Netherlands
47d1b636-33a3-4de7-bf3a-7fa44205909e	Germany
8127a87e-3635-4762-a944-d1e413bda66c	Croatia
9512417d-4dd0-42dd-85a6-2bad9a2c5227	Czech Republic
ebbcdac6-d783-4ef6-aec2-bb6cd4eb5d4b	Poland
9c4145ac-9701-42eb-a9b7-96a1bda4642c	Netherlands
34979ea6-1d69-42bb-9f04-d92e604756b5	Netherlands
601eb18e-71f9-4bab-97a2-d671fb148cd7	Estonia
fc2c0b97-494f-4a2b-aa3d-066f3304fca2	Greece
90e38c19-0883-4c5d-8120-cba054768065	Portugal
5b8264e6-3628-41f1-a0a8-ba6d837e0f5a	Bulgaria
f8372a36-bb14-4f2e-81c8-3180ab69367c	Sweden
341ca2ee-895e-4563-b591-272733f2f06b	France
0ab4f341-db89-41d2-8f72-8d45b8421388	Sweden
7eba0fb8-cd03-4e10-a726-06883cfc36b4	Poland
380e1957-1bbb-40f2-aa62-e2c21ca3fee5	Germany
1b37528a-776b-46b9-bea8-5ee1c305a03b	Germany

Popular Downloads

Data Sheet, Technical Information	4NWD004445_ML
Instructions and Manuals	4NWD004445_ML

Environmental

Ambient Air Temperature	Storage -15...+60 °C
Environmental Information	No declaration needed

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85044000
E-Number (Norway)	6600713
Country or Territory of Origin	China

Dimensions

Product Net Width	122 mm
Product Net Height	160 mm
Product Net Depth / Length	315 mm
Product Net Weight	4.7 kg

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	197 mm
Package Level 1 Height	250 mm
Package Level 1 Depth / Length	395 mm
Package Level 1 Gross Weight	6 kg
Package Level 1 EAN	7640169262616

Technical

Apparent Power Output	800 V·A
Battery Chemical Composition	Lead-Acid
Battery Type	Portable
Battery Weight	2.5 kg
Communication Interface	USB, RS-232
Connection Type	IEC C14
Display Type	LCD
Input Voltage (U_{in})	230 V
Input Voltage Type	AC
Number of Batteries	1
Number of Outputs	C13 Connection 4
Number of Phases	1-phase Primary 1-phase Secondary
Options Provided	Auto shut down function
Rated Frequency (f)	Primary 50 Hz Primary 60 Hz Secondary 50 Hz Secondary 60 Hz
Rated Output Power	480 W

Certificates and Declarations

Declaration of Conformity - CCC	No certification needed
Declaration of Conformity - CE	4NWD004317

External Classifications and Standards

ETIM 9	EC000382 - UPS
ETIM 10	EC000382 - UPS
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business
CN8	85044000
eClass	V11.1 : 27040690
Object Classification Code	G

Categories

UPS, Power Conditioning and Power Distribution → UPS → Single-Phase UPS → PowerValue 11 LI IEC 230V

