



PRODUCT-DETAILS

UPS PowerValue 11LI Pro 800 VA

UPS PowerValue 11LI Pro 800 VA



General Information	
Extended Product Type	UPS PowerValue 11LI Pro 800 VA
Product ID	4NWP100176R0001
EAN	7640169262661
Catalog Description	UPS PowerValue 11LI Pro 800 VA
Long Description	VI UPS PowerValue 11LI Pro 800VA/480W;230V;50/60Hz;pure sinewave;2.5 min

Material Compliance	
Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	4NWD004620
RoHS Information	4NWD004322
RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
SCIP	424cab99-027a-4c83-bed6-c736eef883ff Switzerland
Simplified SCIP	bceddeb9-4635-4e40-a559-0d58656cd9ec Germany bdaefabb-71cd-44b1-96f1-ecfa49f3ff34 Netherlands a06a9ce3-b60f-4ade-87ce-65956b949e95 Germany f30e2997-56e2-4141-8774-7f7165ea6bb6 Croatia abe0cc33-793b-4193-a3d4-e3ebf5e8a55b Denmark f06baa1b-34f7-4b14-850f-9c0bb7956c1c Czech Republic

f490c704-346f-43b0-8503-8cd628116384	Poland
4f94c215-4216-4958-98d6-c044cde00f3f	Netherlands
be5788d1-b127-460f-b65b-7c0312edc67b	Netherlands
cda211ec-8567-44f1-89fb-3cf62bc53d52	Estonia
5e91bd56-1daf-4da9-a3e8-02d473423479	Greece
3475bbec-c17a-46a7-bb5f-6fcd777e1b0	Portugal
59ad7310-57ad-44d8-8ef3-aff4e4ee8c42	Bulgaria
efd9abcd-406e-4557-b2bf-76e4a5a7c5bb	Sweden
240c340d-5811-4f0c-a440-de77baa0a00f	France
697fe351-1c70-49f7-acdb-4823ebdb16a0	Sweden
3895262b-0480-4244-89e2-26c731cdd1a8	Poland
acaf8901-1982-43d4-9d17-2269d2c5175e	Germany
5b3f2b17-8ca5-4894-be26-8dbc02ffe7d	Germany
537f45e4-b9a8-4572-a9fb-3468afec4eaa	France
a6f4e02b-97ca-4dc6-860a-65844f5f0154	Netherlands
72061038-c282-4ea6-bb32-d7405f57a3f1	Spain
570930bb-88c7-4e02-99b1-1e552da09640	Germany
ad7b2971-75a4-4e59-94ff-13925fabf230	Poland
0cfc0132-8efa-4475-a472-272544e7443e	Norway
057e83c8-aa62-486c-a8d6-11a901005545	Finland
e6ab87b1-ecab-476c-a5fe-3486a0147b7a	Netherlands

Popular Downloads

Data Sheet, Technical Information	4NWD004444_ML
Instructions and Manuals	4NWD004444_ML

Environmental

Ambient Air Temperature	Storage -15...+60 °C
Environmental Information	No declaration needed

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85044000
E-Number (Finland)	8408630
E-Number (Norway)	6600718
Country or Territory of Origin	China

Dimensions

Product Net Width	10 mm
Product Net Height	145 mm
Product Net Depth / Length	328 mm
Product Net Weight	6.6 kg

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	140 mm
Package Level 1 Height	228 mm
Package Level 1 Depth / Length	385 mm
Package Level 1 Gross Weight	7.9 kg
Package Level 1 EAN	7640169262661

Technical	
Apparent Power Output	800 V·A
Battery Chemical Composition	Lead-Acid
Battery Type	Portable
Battery Weight	2.5 kg
Communication Interface	USB, RS-232
Connection Type	IEC C14
Display Type	LCD
Input Voltage (U _{in})	230 V
Input Voltage Type	AC
Number of Batteries	1
Number of Outputs	C13 Connection 4
Number of Phases	1-phase Primary 1-phase Secondary
Options Provided	Auto shut down function
Rated Frequency (f)	Primary 50 Hz Primary 60 Hz Secondary 50 Hz Secondary 60 Hz
Rated Output Power	480 W

Certificates and Declarations	
Declaration of Conformity - CCC	No certification needed
Declaration of Conformity - CE	4NWD004322

External Classifications and Standards	
ETIM 9	EC000382 - UPS
ETIM 10	EC000382 - UPS
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business
CN8	85044000
eClass	V11.1 : 27040690
Object Classification Code	G

Categories	
UPS, Power Conditioning and Power Distribution → UPS → Single-Phase UPS → PowerValue 11 LI IEC 230V	

