

Features

- Test battery testing ranges from 100 to 2000 CCA
- Detects bad cells
- Tests deep discharge battery
- Protects against reverse polarity
- Multiple battery rating systems: CCA, JIS, EN, DIN, SAE, IEC
- Tests ordinary lead acid battery, AGM flat plate battery, AGM spiral battery, and GEL battery etc.
- 2.4"TFT color display, resolution 240(RGB) x 320 Pixels

RS PRO Battery Testers

RS Stock No.: 0285512



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

This Battery Tester easily and accurately measures the cold cranking amps capability of the vehicle starting battery, healthy state of the battery itself, and common fault of the vehicle starting system and charging system. This helps to locate the problem quickly and accurately, thus to achieve quick vehicle repair.

General Specifications

For Battery Chemistry	Lead Acid
Display	2.4" TFT 240*320 pixels colour LCD display
Operating Temperature	0 to 50°C
Storage Temperature	-20 to 70°C
Power	Provided via cable from car battery

Mechanical Specifications

Dimensions	784mm x 355mm x 210mm
Length	784mm
Width	355mm
Height	210mm
Weight	293g

Measurement

Measure Standard	Measure Range
CCA	100~2000
BCI	100~2000
CA	100~2000
MAC	100~2000
JIS	26A17—245H52
DIN	100-1400
IEC	100-1400
EN	100-2000
SAE	100-2000
GB	100-2000

Approvals

Declarations	CE
--------------	----