

Product datasheet

Specifications

Actassi 19-C Patch Panel Sliding Evo 19" 1U 24pt S-One STP Cat6



VDIG118241B60

Main

range of product	Actassi
Product or component type	Equipped sliding 19" data panel
Device presentation	Loaded
Provided equipment	1 rear cable organizer 4 label holders 24 RJ45 connectors 2 quick fix 19" mountings 24 light grey shutters
Colour	Dark grey (RAL 7016)
Additional information	Automatic grounding

Complementary

Variant	Evolution
Number of port	24 port of STP
Communication network category	6
Cover type	Screened
Mounting support	19" rack
Number of rack unit	1U
Type of connector	S-One
Material	DC01 metal sheet 1.2 mm PA6 plastic part PA66 GF20 plastic part
Width	490 mm
Depth	240 mm
Height	47 mm
Net weight	2.9 kg

Environment

Ambient air temperature for operation	-10...55 °C
Standards	IEC 60297 ISO/IEC 11801:ed. 2.2, 2011 NF C 20-150

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Height	6.0 cm
Package 1 Width	26.8 cm
Package 1 Length	55.0 cm
Package 1 Weight	3.009 kg
Unit Type of Package 2	S04
Number of Units in Package 2	6
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	18.831 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Total lifecycle Carbon footprint	30
----------------------------------	----

Use Better

Materials and Substances

Packaging made with recycled cardboard	No
--	----

Packaging without single use plastic	No
--------------------------------------	----

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
-----------------------------------	--

REACH Regulation	REACH Declaration
------------------	-----------------------------------

Halogen-free status	Halogen free product
---------------------	----------------------

PVC free	Yes
----------	-----

Use Again

Repack and remanufacture

End of life manual availability	No need of specific recycling operations
---------------------------------	--

Take-back	No
-----------	----