



# — PRODUCT DATA SHEET

## iW5R-FLEX Inspection Lamp 600 (Box)



# iW5R flex

## PRODUCT DESCRIPTION

Finally: The iW5R flex mini floodlight ensures a clear view and free hands, even when working in extremely tight conditions such as cable shafts and engine compartments. In addition to its compact dimensions and flexible attachment options by magnetic holder and hook, the compact floodlight scores points thanks to a folding LED lamp head which illuminates even the tightest crevices directly from the inside - with up to 600 powerful lumen<sup>1</sup>.

- Folding, slim lamp head for inaccessible spaces
- Chip-on-Board technology for even light distribution
- Light options: focused spot light and broad work light
- USB charging
- Two brightnesses with a luminous flux of up to 600 lumen<sup>1</sup>
- 7-Year with registration warranty for complete peace of mind



### TECHNICAL DATA

Width [mm]	40
Depth [mm]	32
Height [mm]	151
Weight incl. batteries [g]	220
Focus function	No
Primary material	Other plastics
Cartridge	No

### POWER SUPPLY

Power source type	Rechargeable battery
Battery quantity	1
Battery type	L-ion
Battery description	18650 3.7V
Total battery voltage [V]	3.7
Total battery capacity [mAh]	2600
Rechargeable	Yes
UN number	UN 3481
Charging time <sup>5</sup> [min]	240
Energy status indicator	Battery Indicator, Charge Indicator

### FURTHER SPECIFICATIONS

IP class	IP30
Working temperature range [°C]	-10 to +40

### LIGHT FUNCTIONS

Low Power, Power
------------------

LIGHT SOURCE	Flood	Spot
Amount LEDs	1	1
LED type	12W COB LED	Power LED
Colour	White	White
Colour Temperature [K]	5400 to 6600	5400 to 6600
Colour Rendering Index (CRI)	80	70

### LEDLENSER VALUES - Flood

	Boost	Power	Mid Power	Low Power
Light output <sup>1</sup> [lm]		600		250
Beam distance <sup>1</sup> [m]				
Run time <sup>1</sup> [h]		2		4

### LEDLENSER VALUES - Spot

	Boost	Power	Mid Power	Low Power
Light output <sup>1</sup> [lm]		100		
Beam distance <sup>1</sup> [m]				
Run time <sup>1</sup> [h]		6.5		

### SWITCH

Switch
--------

# iW5R flex

## PACKAGING AND LOGISTICS



### PACKAGING INFORMATION

Type of packaging	Box
Scope of delivery	USB cable, USB power supply
Item No.	502006
Customs tariff number	85131000
Colour	black

### SINGLE PACKAGE

Dimensions W x H x D [cm]	87 x 163 x 50
Gross weight [g]	372
GTIN-13	4058205016353

### INNER CARTON

Unit	6
Dimensions W x D x H [cm]	181 x 158 x 172
Gross weight [g]	2358
GTIN-13	4058205016360

### EXPORT CARTON

Unit	24
Dimensions W x D x H [cm]	385 x 365 x 190
Gross weight [kg]	9.97
GTIN-13	4058205016377

# iW5R flex

## FOOTNOTES

The information pertaining to scope of delivery, appearance, performance, dimensions and weight corresponds to the information available at the time of publication. In the interest of product development, we reserve the right to change scope of delivery, appearance, design and color without prior notice. Product images may vary from the actual products and may show optional accessories which can be purchased separately. Errors and omissions excepted.

1) Measurements according to ANSI FL1 on the respective setting. Average values, in some cases, deviations by +/- 15 % may occur due to technical reasons. If no setting is explicitly indicated, the values refer to luminous flux (lumens/lm) and lighting range (meters/m) on the highest setting and to battery duration (hours/hrs/h) on the lowest setting. A boost function (if available) can be used several times, but only for short periods of time. If no setting is explicitly indicated, measurement is based on "energy saving mode."

2) Calculated capacity value in watt-hours (Wh). This applies to the delivery state of the battery/ies inside the respective item, or for lights with rechargeable battery/ies, to the rechargeable battery/ies inside the product when fully charged.

4) Warranty period of five years from the date of purchase, seven years if the product is registered online on our website. The warranty is valid worldwide and legal warranty rights also apply. It covers defects in materials and workmanship. For the proper functioning of rechargeable batteries a different warranty period of 24 months applies. Excluded from this warranty are the products of the "Solidline" series, Ledlenser K1 and Ledlenser K2. The warranty does not apply to defects in batteries, holsters, pouches, remote switches, color filters, imprints or surface coatings. The guarantor is Ledlenser GmbH & Co. KG, Kronenstr. 5 - 7, 42699 Solingen, Germany. More information: [ledlenser.com/warranty](http://ledlenser.com/warranty)

5) Charging time varies by hardware used.