

Multi Function Power Head XGT®

UX01G

40V max • 0 - 9 700 min⁻¹

Powerful cordless XGT® Multi function power head

UX01G has a High/Medium/Low 3-speed selection and variable speed control by trigger. Multi-tool system consisting of power head and versatile optional attachments is ideal for a wide range of applications.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Brushless Motor	✓
No load speed	0 - 5700 / 8200 / 9700 min ⁻¹
International Protection Class (IP)	IPX4
Sound Power Level (L _{WA})	86,6 - 104,1 dB(A)
Sound Pressure Level (L _{pA})	76,1 - 100 dB(A)
Noise Uncertainty (K Factor)	0,2 - 3 dB(A)
Product Dimensions (L x W x H):	1001 x 320 x 209 mm
Tool weight with battery	5,3 - 12,5 kg
Product net weight	3,5 kg
System	2123
Handle Type	O

User benefits

- Ergonomically designed new loop handle fits comfortably in user's hand
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- Battery protection system automatically shuts off power when the battery level is low
- 3-speed options (Low / Medium / High) allows the operator to match speed to application
- Variable speed control by trigger

Link to product - www.makita.uk.com



Related products

Optional AC

125516-5

Band assembly



127508-0

Band Assembly



1912G3-7

Shear Blade Assembly 500



1912R8-4

UB402MP BLOWER ATTACHMENT



1912T8-8

Hedge Trimmer Attachment Set



1912V6-6

Shear Blade Assembly 330 Set



1913C9-3

Ground Trimmer Attachment Set



191E24-8

Shaft extension attachment



191M56-3

Rotary scissor attachment, EM407MP



191N31-5

Grass trimmer attachment, 300 mm,



191P72-3

Blower attachment, UB401MP



191T38-7

Pole Saw Attachment, 300 mm, 1/4",



195638-5

Soft Carrying Bag 1200 x 330 x 300



196256-2

Split Shaft Attachment



196752-0

Edger Attachment



198768-1

Brush cutter attachment set



198779-6

String Trimmer Attachment



198893-8

Trimmer Head 2,0 mm, M10 x 1.25



199318-5

Roller brush attachment



199339-7

Roller sweeper attachment



783202-0

Hex Wrench 4Mm



831304-7

Accessory Bag



D-66008

4-Tooth Blade, 230 x 25,4 mm



DEAPF400MP

Split Shaft Water Pump Attachment



Other

[User manual](#)

[Parts drawing](#)