



PRODUCT DATASHEET

Datasheet creation date: 2025/06/02 9:22 (UTC)



7313BEAT85

Single-Row Angular Contact Ball Bearings

Boundary Dimensions

d	65	mm	Bore diameter
D	140	mm	Outside diameter
B	33	mm	Width
r (min.)	2.1	mm	Chamfer dimension
r1 (min.)	1.1	mm	Chamfer dimension

Basic Load Ratings

Cr	119000	N	Basic dynamic load rating
C0r	77000	N	Basic static load rating

Speeds

Grease	4300	min-1	Grease lubrication
Oil (Oil-bath)	6300	min-1	Oil-bath lubrication

Dimensions

a	59.5	mm	Effective load center
---	------	----	-----------------------

Abutment and Fillet Dimensions

da (min.)	77	mm	Diameter of shaft abutment
Da (max.)	128	mm	Diameter of housing abutment
ra (max.)	2	mm	Radius of shaft or housing fillet

Mass

Mass approx.	2.09	kg	Mass approx.
--------------	------	----	--------------

