

## FEATURES

- Plan Shank
- Various lengths
- HSS for performance and safety
- Perfect for general workshop and maintenance use

## RS PRO HSS Twist Drill Bit, 9mm x 125mm

RS Stock No.: 213-102



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

Brought to you by RS PRO, a range of jobber drill bits suitable for high-speed metal, wood and plastic drilling. Designed as a twisted drill bit, these attachments guarantee excellent performance and will be an asset to your application. All models are highly reliable and excellent quality.

## General Specifications

<b>Drill Bit Type</b>	Twist Drill Bit
<b>Type</b>	Twist
<b>Material</b>	HSS M2
<b>Drilling Application</b>	Construction, electrical or masonry applications

## Mechanical Specifications

<b>Overall Length</b>	125mm
<b>Point Angle</b>	118°
<b>Diameter</b>	9mm
<b>Flute Length</b>	81mm

## Approvals

<b>Compliance/Certifications</b>	DIN 338
----------------------------------	---------



RS Stock No.	Diameter(mm)	Overall Length (mm)	Flute Length (mm)
<a href="#">212-991</a>	1.0	34	12
<a href="#">212-985</a>	1.5	40	18
<a href="#">212-979</a>	2.0	49	24
<a href="#">213-089</a>	2.5	57	30
<a href="#">212-963</a>	3.0	61	33
<a href="#">212-957</a>	3.3	65	36
<a href="#">213-073</a>	3.5	70	39
<a href="#">213-067</a>	4.0	75	43
<a href="#">213-051</a>	4.2	75	43
<a href="#">213-023</a>	4.5	80	47
<a href="#">213-045</a>	5.0	86	52
<a href="#">213-039</a>	5.5	93	57
<a href="#">213-095</a>	6.0	93	57
<a href="#">213-168</a>	6.5	101	63
<a href="#">213-146</a>	7.0	109	69
<a href="#">213-130</a>	7.5	109	69
<a href="#">213-124</a>	8.0	117	75
<a href="#">213-118</a>	8.5	117	75
<a href="#">213-102</a>	9.0	125	81
<a href="#">212-929</a>	10.0	133	87
<a href="#">212-913</a>	10.2	133	87
<a href="#">212-907</a>	10.5	133	87
<a href="#">212-884</a>	11.0	142	94
<a href="#">212-878</a>	12.0	151	101
<a href="#">212-935</a>	13.0	151	101