

Features

- Lightweight and flexible
- Blue colour
- Length 25m

RS PRO Hose Pipe

RS Stock No.: 146-7730, 146-7731, 146-7732,
146-7733



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Blue water hose for use where a flexible, hard-wearing, weather and ozone-resistant hose is required.

We recommend crimp-on-fittings to be used with this hose.

General Specification

Brand	RS PRO
Features	Flexible
Materials	EPDM
Colour	Blue
Length	20m
Suitable Applications	Air, Water
Maximum Operating Temperature	+140°C
Minimum Operating Temperature	-30°C
Maximum Working Pressure	Red 17 bar, Black 7 bar
Hose Pipe Action	Transfer
Bend Radius	65mm

Products in series

Stock No.	Length	Inner Diameter	Outer Diameter	Colour
146-7730	20m	9,5mm	16,5mm	Blue
146-7731	20m	12,7mm	21,5mm	Blue
146-7732	20m	19mm	27mm	Blue
146-7733	20m	25mm	35mm	Blue