

1m DisplayPort 1.2 Cable with Latches M/M – DisplayPort 4k

Product ID: DISPL1M



The DISPL1M 1m DisplayPort™ 1.2 Cable with latches provides a secure, connection between your DisplayPort-equipped devices and is capable of providing higher performance than either HDMI® or dual link DVI.

The DP cable supports high resolutions of up to 4k x 2k (4096 x 2160) @ 60Hz with a maximum HBR2 bandwidth of 21.6 Gbps. The cable also supports Multi-Stream (MST) for daisy chaining multiple monitors and provides optional audio support.

The DISPL1M is backed by StarTech.com's Lifetime Warranty, for guaranteed reliability and ensures that digitally protected content is displayed properly, with both HDCP and DPCP capability.

Certifications, Reports and Compatibility



Applications

- Connecting a DisplayPort Display to a PC or other DisplayPort Source

Features

- High-resolution support of up to 4k x 2k
- Support for High Bit Rate 2 (HBR2) bandwidth of up to 21.6 Gbps
- Backward compatible with DisplayPort 1.1
- Designed and manufactured to DisplayPort 1.2 standards
- Supports the DPCP (DisplayPort Content Protection) standard in addition to HDCP
- Molded latching connectors with strain relief

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
	Fire Rating	CMG Rated (General Purpose)
	Number of Conductors	19
Connector(s)	Connector A	1 - DisplayPort (20 pin) Latching Male
	Connector B	1 - DisplayPort (20 pin) Latching Male
Physical Characteristics	Cable Length	1 m [3.3 ft]
	Cable OD	7.3 mm [0.3 in]
	Color	Black
	Connector Style	Latching
	Product Height	12.800
	Product Length	1 m [3.3 ft]
	Product Weight	85 g [3 oz]
	Product Width	20.900
	Wire Gauge	28 AWG
Packaging Information	Package Quantity	1
	Shipping (Package) Weight	90 g [3.2 oz]
What's in the Box	Included in Package	1 - 1m Latching DisplayPort 1.2 Cable

Product appearance and specifications are subject to change without notice.