

HYDRAULIC SERVICE JACK 3T FOR CARS AND COMMERCIAL VEHICLES



2550 A

PROMO

- Steel structure
- Versatile and compact for use in narrow spaces
- High capacity for use on cars, SUVs and vans
- Dual pump system to lift the car faster
- Equipped with manual descent control
- Air bleed valve, to avoid risk of over-load
- Handle with rubber bumper
- Polyurethane wheels
- Rubber disk: code DL.32A-10
- Front wheels (2 pieces): code DL.32A-1
- Rear wheels (2 pieces): code DL.32A-9

Capacity (t)	3
Min lifting height (mm)	133
Max lifting height (mm)	465

Family details

Code	LxP mm	Weight kg	Quantity for packaging
U25500001	615x344	30,5	1

Stanley Black & Decker Italia S.r.l.

Sede legale: Via Energy Park 6 - 20871 Vimercate (MB)
Sede operativa: Via Volta 3 - 21020 Monvalle (VA) Italia
Partita IVA e C.F.: 03225990138

StanleyBlack&Decker

Società a Socio Unico soggetta a coord. e controllo da parte di Stanley Black & Decker, Inc.
Capitale Sociale I.V. € 12.000.000