

CARATTERISTICHE

- Ideale per la pulizia e la riparazione di filettature danneggiate o corrose
- Struttura HSS dei pezzi
- Taglio facile e pulito dei metalli
- Può essere utilizzato con una chiave per maschiatura o un utensile elettrico
- Ogni pezzo è etichettato nella pratica custodia

Set di maschi con punta a spirale HSS M12 RS Pro

Codice RS: 668-1119



un prezzo eccezionale.

I prodotti firmati RS approvati per impieghi professionali offrono componenti di qualità professionale in tutte le categorie di prodotti. La nostra gamma di prodotti è stata testata da ingegneri e offre una qualità paragonabile a quella dei marchi leader senza pagare

DESCRIZIONE del

Gamma di set di maschi manuali RS Pro. Questo set di alta qualità è dotato di tutte le apparecchiature e gli accessori essenziali necessari per pulire o tagliare con successo nuove filettature su dispositivi di fissaggio, fori e molto altro ancora. Il materiale HSS (acciaio ad alta velocità) rende più facile il taglio di materiali più duri con precisione ed efficienza, pertanto questo set è ideale per l'artigianato professionale o applicazioni di ingegneria generale e nel settore automobilistico.

Specifiche generali

Dimensione filettatura	M12
Tipo	Maschi per filettatura
Filettatura standard	Metrico
Sommario	Maschi: 3 x M3; M4; M5; M6; M8; M10; M12, stampi rotondi: m3; M4; M5; M6; M8; M10; M12 (25 x 9 mm), maschio Chiave: 1-1/2 poll., portafiliera: 25 x 9mm, cacciavite
Numero di pezzi	32
Standard	Metrica ISO
Applicazioni	Applicazioni e riparazioni nel settore automobilistico, officine di manutenzione generale, fai da te, riparazione di macchinari

Specifiche meccaniche

Materiale	HSS
Dimensione massima maschiatura	M12
Dimensione minima maschiatura	M3



RS STOCK NUMBER	MANUFACTURE PART NO.	DESCRIPTION	CONTENT
6681113	T9705	7PC HSS LEFT HAND TAP SET	ISO HSS Taps as Follows: M3, M4, M5,M6,M8,M10,M12, Left Hand, Metric Coarse,Second Tap Package: Red Metal Box
6681119	T9221	22PC HSS TAP SET	ISO HSS Taps as Follows, 3pcs per each size: M3, M4, M5,M6,M8,M10,M12; metric Coarse 1pc Tap Wrench: No.1 1/2 (M5-M12, 3/16"-1/2") Package: Red Metal Box
6681125	T9322	32PC HSS TAP AND DIE SET	21pcs DIN352 HSS Taps as Follows, 3pc each size : M3, M4, M5,M6,M8,M10,M12 7pcs DIN 223 HSS Round Dies 25X9mm, without split as Follows: M3, M4, M5,M6,M8,M10,M12 1pc Tap Wrench: No.1 1/2 1pc Die Holder 25X9mm 1pc Screwdriver Package: Grey Metal Box
6681138	T9323	32PC HSS TAP AND DIE SET	21pcs DIN352 HSS Taps as Follows, 3pc each size : M3, M4, M5,M6,M8,M10,M12 7pcs DIN 223 HSS Round Dies 25X9mm, without split as Follows: M3, M4, M5,M6,M8,M10,M12 1pc Tap Wrench: No.1 1/2 1pc Die Holder 25X9mm 1pc Screwdriver Package: Grey Blow Mold Case
6681122	T9442	44PC HSS TAP AND DIE SET	21pcs DIN352 HSS Taps as Follows, 3pc each size : M3, M4, M5,M6,M8,M10,M12 7pcs DIN 223 HSS Round Dies, without split as Follows: M3, M4, M5,M6,M8,M10,M12 7pc HSS Drills:2.5,3.3,4.2,5.0,6.8,8.5,10.2mm 2pcs Tap Wrench: No.1, No.2 5pcs Die Holder: No.1, No.2,No.3, No.4, No.5 1pc Screw Pitch 1pc Screwdriver Package: Grey Metal Box
6681129	T9540	54PC HSS TAP AND DIE SET	33pcs DIN352 HSS Taps as Follows, 3pc each size : M3, M4, M5,M6,M8,M10,M12,M14,M16,M18,M20 11pcs DIN 223 HSS Round Dies, without split as Follows: M3, M4, M5,M6,M8,M10,M12,M14,M16,M18,M20 2pcs Tap Wrench: No.1, No.3 6pcs Die Holder: No.1, No.2,No.3, No.4, No.5, No.6 1pc Screw Pitch 1pc Screwdriver Package: Grey Metal Box

RS STOCK NUMBER	MANUFACTURE PART NO.	DESCRIPTION	CONTENT
6681113	T9705	7PC HSS LEFT HAND TAP SET	ISO HSS Taps as Follows: M3, M4, M5,M6,M8,M10,M12, Left Hand, Metric Coarse,Second Tap Package: Red Metal Box
6681119	T9221	22PC HSS TAP SET	ISO HSS Taps as Follows, 3pcs per each size: M3, M4, M5,M6,M8,M10,M12; metric Coarse 1pc Tap Wrench: No.1 1/2 (M5-M12, 3/16"-1/2") Package: Red Metal Box
6681125	T9322	32PC HSS TAP AND DIE SET	21pcs DIN352 HSS Taps as Follows, 3pc each size : M3, M4, M5,M6,M8,M10,M12 7pcs DIN 223 HSS Round Dies 25X9mm, without split as Follows: M3, M4, M5,M6,M8,M10,M12 1pc Tap Wrench: No.1 1/2 1pc Die Holder 25X9mm 1pc Screwdriver Package: Grey Metal Box
6681138	T9323	32PC HSS TAP AND DIE SET	21pcs DIN352 HSS Taps as Follows, 3pc each size : M3, M4, M5,M6,M8,M10,M12 7pcs DIN 223 HSS Round Dies 25X9mm, without split as Follows: M3, M4, M5,M6,M8,M10,M12 1pc Tap Wrench: No.1 1/2 1pc Die Holder 25X9mm 1pc Screwdriver Package: Grey Blow Mold Case
6681122	T9442	44PC HSS TAP AND DIE SET	21pcs DIN352 HSS Taps as Follows, 3pc each size : M3, M4, M5,M6,M8,M10,M12 7pcs DIN 223 HSS Round Dies, without split as Follows: M3, M4, M5,M6,M8,M10,M12 7pc HSS Drills:2.5,3.3,4.2,5.0,6.8,8.5,10.2mm 2pcs Tap Wrench: No.1, No.2 5pcs Die Holder: No.1, No.2,No.3, No.4, No.5 1pc Screw Pitch 1pc Screwdriver Package: Grey Metal Box
6681129	T9540	54PC HSS TAP AND DIE SET	33pcs DIN352 HSS Taps as Follows, 3pc each size : M3, M4, M5,M6,M8,M10,M12,M14,M16,M18,M20 11pcs DIN 223 HSS Round Dies, without split as Follows: M3, M4, M5,M6,M8,M10,M12,M14,M16,M18,M20 2pcs Tap Wrench: No.1, No.3 6pcs Die Holder: No.1, No.2,No.3, No.4, No.5, No.6 1pc Screw Pitch 1pc Screwdriver Package: Grey Metal Box