

Eaton 17.5THMEJ100

Catalog Number: 17.5THMEJ100

Eaton Bussmann series medium voltage DIN fuse, 100 A, AC 17.5 kV, 2.5", 64 x 442 mm, backup, DIN, with striker



General specifications

Product Name	Catalog Number
Eaton Bussmann series medium voltage DIN fuse	17.5THMEJ100
	UPC
	051712186261
EAN	Product Length/Depth
5027590246026	442 mm
Product Height	Product Width
66 mm	64 mm
Product Weight	Warranty
3700 g	Not Applicable
Compliances	
DIN 43625	
VDE 0670-4	
IEC 60282-1	

Product specifications

Used with

270303 Fuse clip

A3354720 Fuse clip

Type

Fuse

Application

transformer protection

indoor or outdoor use

Amperage Rating

100 A

Fuse indicator

With Striker

Fuse size

64 x 442 mm

Breaking capacity

50 kA

Installation technique

Air

Performance Cat According To IEC 60282-1

Back-up

Product application

Primary side transformer protection

Rated frequency - max

50 Hz

Rated frequency - min

50 Hz

Release characteristic

Other

Standard

DIN

Utilization category

Other

Voltage type

AC

With striker

Resources

Catalogs

Bussmann series complete full line catalog no. 1007

17.5THMEJ100~17-5THMEJ100~17.5KV 100A 2.5DIN BROWN
RESINSEAL FUSE

Technical data sheets

720104 12kV DIN medium voltage fuses

720105 17.5kV DIN medium voltage fuses

720106 24kV DIN medium voltage fuses

Yes

Class

Class back-up

Barrels

1

Pre arc (I2T)

2 x 10000

Resistance

8.38 Ohms

Watt losses

127 W

Fuse diameter

64 mm

Interrupt rating

50 kAIC

Construction size

64 x 442 mm

Mounting method

Clip-in

Packaging type

Standard

Voltage rating

17.5 kV

Fuse type

THMEJ



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia