

# KERN JIT 100

**KERN**

Infrared thermometer for industry, environmental engineering and maintenance work



Category	
Brand	Sauter
Product category	Environment/ Occupational safety
Product group	Infrared thermometer
Product family	JIT

Measuring System	
Temperature - measuring range 1 [Min]	-32 °C
Temperature - measuring range 1 [Max]	0 °C
Temperature accuracy - measuring range 1	+/- 1,5 °C+0,1 °C/ °C
Temperature repeatability - measuring range 1	+/- 0,7 °C
Temperature coefficient - measuring range 1	+/- 0,1 °C/ °C
Temperature - measuring range 2 [Min]	0 °C
Temperature - measuring range 2 [Max]	100 °C
Temperature accuracy - measuring range 2	+/- 1,5 °C
Temperature repeatability - measuring range 2	+/- 0,7 °C
Temperature coefficient - measuring range 2	+/- 0,1 °C/ °C
Temperature - measuring range 3 [Min]	100 °C
Temperature - measuring range 3 [Max]	420 °C
Temperature accuracy - measuring range 3	+/- 1,5%
Temperature repeatability - measuring range 3	+/- 0,7%

Temperature coefficient - measuring range 3	+/- 0,1% / °C
Level of emission [Min]	0,1
Level of emission [Max]	1
D:S Optic	12:1
Response time	250 ms
Units	°C °F
Temperature [Min] (°C)	-32 °C
Temperature [Max] (°C)	420 °C

Construction	
Dimension (W×D×H)	162×90×48 mm
Material	plastic
Material housing	plastic
Laser power	0,001 W
Laser class	2
Column mount possible	✓

Functions	
Function for averaging	✓
Limit-setting function	✓
Statistic function	✓
Auto-off interval(s) in battery mode/rechargeable battery mode	15 sec

Power Supply	
Supplied power supply	Battery
Battery / accumulator type	Alkali(-Manganese)
Battery	9 V block
Battery connection	9V Bloc
Battery operating time	9 h

Approval	
CE mark	✓

Packing & Shipping	
Delivery time	1 d
Dimensions packaging (W×D×H)	225×110×65 mm
Net weight	0,204 kg
Shipping method	Parcel service
Net weight approx.	0,25 kg
Gross weight approx.	0,35 kg
Shipping weight	0,34 kg

# KERN JIT 100

**KERN**

Infrared thermometer for industry, environmental engineering and maintenance work

## Pictograms

### STANDARD

---

