

HyFlex[®]

ADVANCED MECHANICAL PROTECTION

11-618

Palm coated glove for lightweight applications in dry and slightly oily environments



Multi Purpose Abrasion Protection



Light Duty

Ultra-thin polyurethane gloves, with superb tactility and dexterity, for delicate handling

- **Enhanced dexterity:** HyFlex[®] 11-618 multi-purpose gloves' light 18-gauge liner grants them excellent dexterity, for ease of use and minimal strain
- **Optimized tactility:** These HyFlex[®] gloves' extra thin PU coating delivers optimal tactile sensitivity and a "second skin" feel, ideal for delicate handling
- **Improved durability:** Beyond tactility, their PU coating ensures ANSI/EN-compliant abrasion resistance
- **Considered aesthetics:** HyFlex[®] 11-618 safety gloves' dark nylon liner masks dirt and stains, for long-lasting wear
- **Certified skin-friendliness:** Dermatest[®] certification makes for dermatologically friendly personal protection



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication

Applications

- Picking, fastening components
- Assembling and mounting components
- Fastening components, parts

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-618

Palm coated glove for lightweight applications in dry and slightly oily environments

Key Features

- **Light 18-gauge design:** Industrial gloves with optimal dexterity
- **Thin PU coating:** Tactile sensitivity with a “second skin” feel
- **Dark nylon liner:** Masks dirt and stains, for extended glove life

Vulcanization Chemical Accelerators

- Natural rubber proteins

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance

REACH Compliant



Specifications

| BRAND STYLE | DESCRIPTION | Gauge | SIZE | LENGTH | COATING COLOR | PACKAGE |
|----------------|--|-------|--------------------|-----------------------------|---------------|--|
| HyFlex® 11-618 | Finishing: Palm Coated Coating Material: Polyurethane Liner Material: Nylon Cuff Style: Knitwrist | 18 | 6, 7, 8, 9, 10, 11 | 195-245 mm 7.63-9.96 inches | Black | • 12 pairs in a bag; 12 bags in a carton |

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jaijan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2022 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

