



Product data sheet

Power tools for trade & industry

Cordless Demolition Hammer with SDS max

PRO GSH 18V-5



Cordless freedom with corded performance: SDS max demolition hammer

The most important data

Battery voltage	18.0 V
Impact energy	8.5 J
Impact rate at rated speed	3,050 bpm

Part Number 0 611 918 200

Technical data

Technical data

Impact energy	8.5 J
Impact rate at rated speed	3,050 bpm
Battery voltage	18.0 V
Weight excl. battery	5.3 kg
Tool holder	SDS max
Packaging dimensions (width x length x height)	395 x 607 x 179 mm
BITURBO	Yes
Impact energy nominal	8.5 J

Noise/vibration information

Chiselling in concrete

Vibration emission value ah	13.8 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Cordless freedom with corded performance of 8.5 J thanks to the Brushless technology
- Efficient power-to-weight ratio due to lightweight and compact design, highly optimised drivetrain and powerful impact mechanism
- Optimal tool control with soft start / Adaptive Speed Control (ASC), and lock-on button for continuous chiseling



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

